





Benefits


- ❖ Bellows actuation removes electrical switching from wet environments
- ❖ Ergonomically designed for comfort and ease of use.
- ❖ Lightweight
- ❖ Large soft touch buttons
- ❖ Light operating force
- ❖ Wipe Clean




LABEL OPTIONS




ARROWS



BED UP/DOWN



HEAD UP/DOWN



LEGS UP/DOWN

The herga hand control removes the need for low voltage switching circuits and is suitable for use in wet and hazardous environments.

It is designed to fit comfortably in the hand and its large soft touch buttons allow the control to be operated with the minimum of effort making it ideal for the disabled and infirm.

By removing electrical components from the point of patient care this hand control is designed for medical applications and is currently used on equipment ranging from adjustable beds to patient hoists and bath lifts.

The hand control's all-plastic build makes it robust, yet comfortable and light, and the materials and construction used will meet the requirements of various national and international standards.

Mating bulkhead connectors can be obtained for all hand controls. Refer to accessories page in the main catalogue or contact Herga ref 6418/6419 connectors.

Additional fixture options i.e. internal magnets, can be fitted upon request (non-medical applications).

6450 - -

1. Model Number

2. Body Colour
 A Grey B Black

3. Body
 A With moulded herga logo
 B With printed herga label
 C With printed operation label (select from option 4 below)
 D With blank recess
 E Without label recess

4. Operation Label Options
 A Bed Motif - Head up/down
 B Bed Motif - Bed up/down
 C Bed Motif - Legs up/down
 D Arrows up/down
 Z No label required
Note: Labels can be purchased individually

5. Button Colour
 A Grey B Blue
 C Black D White
 E Red F Green

6. Button Labelling
 A Plain Buttons
 B Buttons With Embossed Arrows

7. Tube Type
 A Grey twin polyurethane 1.5mm bore
 B Grey twin polyurethane curly coil (select option 8F below)

8. Tube Length
 A 2 Metres
 B 3 Metres
 F Curly Coil - Unstretched 0.9M Stretched 2.4M
 Z No tube required
Note: Other tube lengths available upon request

9. Fixture Options
 A Grey Moulded Rigid Plastic Hook
 B Suction Cup
 Z No fixtures required